



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product compatibility	XCKM XCKL
Associated body	ZCKL1 ZCKM8H7 ZCKMD31H7 ZCKLD31 ZCKMD37H29 ZCKM6H7 ZCKM1H29 ZCKLD39 ZCKM9 ZCKMD39H29 ZCKL5H7 ZCKLD35H7 ZCKMD35 ZCKL7H7 ZCKMD37 ZCKL8 ZCKMD35H7 ZCKMD37H7 ZCKLD37 ZCKM7 ZCKM8H29 ZCKL6 ZCKLD39H7 ZCKMD39 ZCKMD31H29 ZCKM7H7 ZCKM5H7 ZCKM1H7 ZCKLD37H7 ZCKM5H29 ZCKM7H29 ZCKM6

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKM8
 ZCKL6H7
 ZCKL1H7
 ZCKLD35
 ZCKL7
 ZCKM1
 ZCKMD35H29
 ZCKM9H29
 ZCKLD31H7
 ZCKM6H29
 ZCKM5
 ZCKMD31
 ZCKMD39H7
 ZCKL5
 ZCKL8H7

Movement of operating head	Rotary
Type of operator	Roller lever spring return metal
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1012 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------