

		min resistor Value	max resistor Value	nominal resistor Value	average power available at 50°C	SE Commercial reference	SE Commercial reference
		ohm	ohm	ohm	kW	braking resistor	braking unit
ATV930U07N4	ATV950U07N4	56	728	100	0.1	VW3A7730	-
ATV930U15N4	ATV950U15N4	56	352	100	0.1	VW3A7730	-
ATV930U22N4	ATV950U22N4	56	236	100	0.1	VW3A7730	-
ATV930U30N4	ATV950U30N4	34	172	100	0.1	VW3A7730	-
ATV930U40N4	ATV950U40N4	34	127	100	0.1	VW3A7730	-
ATV930U55N4	ATV950U55N4	23	91	60	0.16	VW3A7731	-
ATV930U75N4	ATV950U75N4	19	66	60	0.16	VW3A7731	-
ATV930D11N4	ATV950D11N4	12	44	28	0.3	VW3A7732	-
ATV930D15N4	ATV950D15N4	15	32	28	0.3	VW3A7732	-
ATV930D18N4	ATV950D18N4	15	26	16	1.1	VW3A7733	-
ATV930D22N4	ATV950D22N4	15	21	16	1.1	VW3A7733	-
ATV930D30N4	ATV950D30N4	10	16	16	1.1	VW3A7733	-
ATV930D37N4	ATV950D37N4	10	13	10	1.1	VW3A7734	-
ATV930D45N4	ATV950D45N4	10	10.6	10	1.1	VW3A7734	-
ATV930D55N4	ATV950D55N4	2.5	8.7	8	1.1	VW3A7735	-
ATV930D75N4	ATV950D75N4	2.5	6.3	5	1.9	VW3A7736	-
ATV930D90N4	ATV950D90N4	2.5	5.2	5	1.9	VW3A7736	-
ATV930C11N4C		2.5	4.3	2.5	3.2	VW3A7737	VW3A7105
ATV930C13N4C		2.5	3.5	2.5	3.2	VW3A7737	VW3A7105
ATV930C16N4C		2.5	2.9	2.5	3.2	VW3A7737	VW3A7105

	min resistor Value	max resistor Value	nominal resistor Value	average power available at 50°C	SE Commercial reference	SE Commercial reference
	ohm	ohm	ohm	kW	braking resistor	braking unit
ATV930U07M3	44	186	100	0.1	VW3A7730	-
ATV930U15M3	33	90	60	0.16	VW3A7731	-
ATV930U22M3	22	60	60	0.16	VW3A7731	-
ATV930U30M3	22	44	28	0.3	VW3A7732	-
ATV930U40M3	16	32	28	0.3	VW3A7732	-
ATV930U55M3	11	23	16	1.1	VW3A7733	-
ATV930U75M3	8	17	16	1.1	VW3A7733	-
ATV930D11M3	5	11.5	10	1.1	VW3A7734	-
ATV930D15M3	5	8.3	8	1.1	VW3A7735	-
ATV930D18M3	5	6.7	5	1.9	VW3A7736	-
ATV930D22M3	5	5.5	5	1.9	VW3A7736	-
ATV930D30M3	2.5	4.1	2.5	3.2	VW3A7737	-
ATV930D37M3	2.5	3.3	2.5	3.2	VW3A7737	-
ATV930D45M3	2.5	2.7	2.5	3.2	VW3A7737	-
ATV930D55M3C	1.4	2.2	1.4	1.5	VW3A7738	VW3A7106
ATV930D75M3C	1.4	1.6	1.4	1.5	VW3A7738	VW3A7106