



### Main

|                           |  |
|---------------------------|--|
| Range of product          | Harmony XB4<br>Harmony XB5                   |
| Product or component type | Block for test light                         |
| Product compatibility     | BA 9s<br>Integral LED                        |
| Light block type          | Single block for test light function         |
| [Us] rated supply voltage | 12 V AC/DC<br>24 V AC/DC<br>24...120 V AC/DC |
| Electrical connection     | 1 wire                                       |

### Complementary

|                                   |   |
|-----------------------------------|---|
| Electrical shock protection class | Class I for Harmony XB4 conforming to IEC 60536<br>Class II for Harmony XB5 conforming to IEC 60536 |
| Product weight                    | 0.01 kg   |

### Environment

|                                       |   |
|---------------------------------------|---|
| Ambient air temperature for storage   | -40...70 °C   |
| Ambient air temperature for operation | -25...70 °C   |
| Standards                             | EN 60947-1<br>EN 60947-5-1<br>EN 60947-5-4<br>EN 60947-5-5<br>IEC 60947-1<br>IEC 60947-5-1<br>IEC 60947-5-4<br>IEC 60947-5-5<br>JIS C 4520<br>UL 508<br>CSA C22.2 No 14 |
| Product certifications                | BV<br>CSA<br>DNV<br>GL<br>LROS (Lloyds register of shipping)<br>RINA<br>UL listed   |

|                      |  |
|----------------------|--|
| Vibration resistance | 5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6  |
| Shock resistance     | 30 gn for 18 ms conforming to IEC 60068-2-27<br>50 gn for 11 ms conforming to IEC 60068-2-27 |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---

## Wiring Diagram

---

