



ZCK D109

Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Plunger head
Product compatibility	XCKM XCKL
Associated body	ZCKL8 ZCKLD37H7 ZCKM7H29 ZCKM8H29 ZCKMD35H29 ZCKM6 ZCKLD39H7 ZCKM7H7 ZCKM7 ZCKM9H29 ZCKLD31 ZCKLD39 ZCKMD35H7 ZCKM5H29 ZCKMD35 ZCKL1H7 ZCKMD37H7 ZCKL6H7 ZCKM9 ZCKMD37H29 ZCKL7 ZCKM1H29 ZCKL6 ZCKL7H7 ZCKMD31 ZCKLD35H7 ZCKM1 ZCKM5H7 ZCKL5 ZCKL8H7

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKM6H7
 ZCKMD37
 ZCKLD37
 ZCKMD39H7
 ZCKMD31H7
 ZCKM8H7
 ZCKLD35
 ZCKMD39
 ZCKM1H7
 ZCKM8
 ZCKMD39H29
 ZCKMD31H29
 ZCKM5
 ZCKLD31H7
 ZCKM6H29
 ZCKL1
 ZCKL5H7

Movement of operating head	Linear
Type of operator	End plunger spring return metal (with protective boot)
Type of approach	Vertical approach 1 direction

Complementary

Switch actuation	On end
Positive opening	With
Head material	Plastic

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1012 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------