



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product compatibility	XCKL XCKS XCKM
Associated body	ZCKLD35 ZCKL8H7 ZCKSD37 ZCKM5H7 ZCKM5H29 ZCKMD31 ZCKS9H29 ZCKL1H7 ZCKL5 ZCKM8H7 ZCKL8 ZCKLD35H7 ZCKLD37H7 ZCKM8 ZCKS9 ZCKM1H29 ZCKSD35H29 ZCKL1 ZCKM1 ZCKMD31H7 ZCKM9 ZCKSD39H29 ZCKL6H7 ZCKLD31H7 ZCKS5H29 ZCKL7 ZCKMD39H29 ZCKSD39 ZCKS5

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKS1H29
 ZCKS6
 ZCKS2H29
 ZCKSD35
 ZCKS7
 ZCKLD39
 ZCKM9H29
 ZCKMD37H7
 ZCKL5H7
 ZCKMD37
 ZCKMD37H29
 ZCKM5
 ZCKS2
 ZCKLD39H7
 ZCKM6H29
 ZCKSD31H29
 ZCKM7
 ZCKS8H29
 ZCKMD35
 ZCKS1
 ZCKLD37
 ZCKS7H29
 ZCKM1H7
 ZCKM7H29
 ZCKM7H7
 ZCKL6
 ZCKS8
 ZCKM8H29
 ZCKMD39
 ZCKM6
 ZCKLD31
 ZCKM6H7
 ZCKSD31
 ZCKMD31H29
 ZCKL7H7
 ZCKS6H29
 ZCKMD35H29
 ZCKMD39H7
 ZCKSD37H29
 ZCKMD35H7

Movement of operating head	Rotary
Type of operator	Spring rod lever spring return (with metal rod)
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By any moving part
Positive opening	Without
Head material	Plastic

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1022 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------