

ZCKE629

limit switch head ZCKE - steel roller plunger with protective boot



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ7 ZCKJD37 ZCKJ8H29 ZCKJ11H7 ZCKJ1H7 ZCKJ2H7 ZCKJD31H29 ZCKJ11H29 ZCKJ4H29 ZCKJ5 ZCKJ6 ZCKJ9H29 ZCKJD35H7 ZCKJD31 ZCKJ41H7 ZCKJ11 ZCKJ6H7 ZCKJD37H7 ZCKJ21H7 ZCKJ21 ZCKJ1 ZCKJD39H29 ZCKJD37H29 ZCKJD39H7 ZCKJ9H7 ZCKJ8 ZCKJ41H29 ZCKJ41 ZCKJ5H7 ZCKJ1H29 ZCKJD31H7

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJ8H7
 ZCKJ4H7
 ZCKJD35H29
 ZCKJ4
 ZCKJ2
 ZCKJ9
 ZCKJ6H29
 ZCKJ21H29
 ZCKJD39
 ZCKJ2H29
 ZCKJ7H29
 ZCKJ5H29
 ZCKJD35
 ZCKJ7H7

Movement of operating head	Linear
Type of operator	Roller plunger spring return metal (with protective boot)
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1014 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------